



**Terminal, Volta, add.terminal, 3Ph+N, 63A**

Product Datasheet

**Architecture**

Number of poles	2 P
Fixing mode	Snap

**Electric current**

Rated current	63 A
---------------	------

**Materials**

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Transparent	no

**Dimensions**

Height of installed product	38 mm
Length	270 mm
Width of installed product	17 mm

**Connection**

Conductor cross-section (flexible), with wire end sleeve	1,5...25 mm <sup>2</sup>
Conductor cross-section (flexible), without wire end sleeve	1,5...25 mm <sup>2</sup>
Connection cross-section of input and output with screws, for massive conductors	1,5 / 25 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	8 / 15 mm <sup>2</sup>
Type of connection	Quickconnect

**Accessories included**

Closing plate required	no
------------------------	----

**Equipment**

Number of clamp positions	16
---------------------------	----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Safe use in explosive atmosphere	no
----------------------------------	----

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------

VZ428