

quadro automatism

IP65

	Page
Board with internal panel with front insert	3
Board with internal panel with side insert	4
Set of side panels	5
Plain cable entry plate	6
Sliding cable entry plate	7
Accessories	8



FK110

Height 1900mm

Description	Pack qty.	Art No.
Steel enclosure, FK, 1900x600x400 mm	1	FK110
Steel enclosure, FK, 1900x800x400 mm	1	FK120
Steel enclosure, FK, 1900x1000x400 mm	1	FK130
Steel enclosure, FK, 1900x600x500 mm	1	FK111
Steel enclosure, FK, 1900x800x500 mm	1	FK121
Steel enclosure, FK, 1900x1000x500 mm	1	FK131



FK113

Height 2100mm

Description	Pack qty.	Art No.
Steel enclosure, FK, 2100x600x400 mm	1	FK113
Steel enclosure, FK, 2100x800x400 mm	1	FK123
Steel enclosure, FK, 2100x1000x400 mm	1	FK133
Steel enclosure, FK, 2100x600x500 mm	1	FK114
Steel enclosure, FK, 2100x800x500 mm	1	FK124
Steel enclosure, FK, 2100x1000x500 mm	1	FK134

Height 1900mm

Description	Pack qty.	Art No.
Steel enclosure, FK, 1900x600x400 mm	1	FK160
Steel enclosure, FK, 1900x800x400 mm	1	FK170
Steel enclosure, FK, 1900x1000x400 mm	1	FK180
Steel enclosure, FK, 1900x600x500 mm	0	FK161
Steel enclosure, FK, 1900x800x500 mm	0	FK171
Steel enclosure, FK, 1900x1000x500 mm	1	FK181



FK160

Height 2100mm

Description	Pack qty.	Art No.
Steel enclosure, FK, 2100x600x400 mm	1	FK163
Steel enclosure, FK, 2100x800x400 mm	1	FK173
Steel enclosure, FK, 2100x1000x400 mm	1	FK183
Steel enclosure, FK, 2100x600x500 mm	0	FK164
Steel enclosure, FK, 2100x800x500 mm	0	FK174
Steel enclosure, FK, 2100x1000x500 mm	0	FK184



FK163



FK320

Height 1900 and 2100mm

Description	Pack qty.	Art No.
Couple side panels, FK, H1900 D400 mm	1	FK310
Couple side panels, FK, H1900 D500 mm	1	FK311
Couple side panels, FK, H2100 D400 mm	1	FK320
Couple side panels, FK, H2100 D500 mm	1	FK321

Width 600, 800 and 1000mm

Description	Pack qty.	Art No.
Plain cable gland, FK, 600x400 mm	1	FK220
Plain cable gland, FK, 800x400 mm	1	FK230
Plain cable gland, FK, 1000x400 mm	1	FK240



FK220



Width 600, 800 and 1000mm

Description	Pack qty.	Art No.
Plain cable gland, FK, 600x400 mm	1	FK270
Plain cable gland, FK, 800x400 mm	1	FK280
Plain cable gland, FK, 1000x400 mm	1	FK290

FK270

Additional base

Description	Pack qty.	Art No.
Plinth, FK, H100 600x400 mm	1	FK370
Plinth, FK, H100 800x400 mm	1	FK380
Plinth, FK, H100 1000x400 mm	1	FK390
Plinth, FK, H100 600x500 mm	1	FK371
Plinth, FK, H100 800x500 mm	1	FK381
Plinth, FK, H100 1000x500 mm	1	FK391



FK380

Perforated brackets

Description	Pack qty.	Art No.
Pair perforated brackets, FK, D400 mm	1	FK404
Pair perforated brackets, FK, D500 mm	1	FK405



FK404

Association kit

Description	Pack qty.	Art No.
Horizontal coupling kit, Quadro5	1	FM635
Adhesive gasket, quadro	1	FN951



FM635

Fixing and transport

Description	Pack qty.	Art No.
Couple wall mounting brackets, Quadro5	1	FM640
Couple transport lug, Quadro5	1	FM653



FM640

Locking inserts for standard lock

Description	Pack qty.	Art No.
Couple leave lock insert, Venezia, 3 mm	10	10962

Weatherproof handle

Description	Pack qty.	Art No.
Rotary waterproof handle, Quadro5, IP54	5	FZ680



FZ680



FL75Z

Locking inserts

Description	Pack qty.	Art No.
Triangular insert lock, Orion.Plus, 8mm	5	FL74Z
Leave lock insert, Orion.Plus, 3 mm	5	FL75Z
Insert lock, Orion.Plus, 8x8 mm	5	FL76Z
Pair inserts for key, Orion.Plus	1	FL98Z