WNC025

cubyko PB 1F w. FPL wall M grey

Product Datasheet

Architecture

Type of order	push button
Type of control unit	Push button
Number of keys	1
Fixing mode	Screwed

Controls and indicators

Indicator lamp	yes

Main electrical features

Nominal voltage	24V
Frequency	50/60 Hz

Electric current

Rated current	10 A

Capacity

Number of modules for WA	2

Materials

Colour	complete grey
RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Polypropylen
Type of surface treatment	mat

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x77
Width of installed product	75 mm

Installation, mounting

Fixing type	With screws
Mounting type	surface

Connection

Connection cross-sect. rigid cable	mini 2x1 mm² - maxi 2x2,5 mm²
Type of contacts	1NC+1NO
Type of connection	Quickconnect

Standards

Approvals	EN 60669-1

Safety

IK protection code against mecanical impacts	07
Protection index IP	IP55

Use conditions

Operating temperature	-15…30 °C
Storage/transport temperature	-50…50 °C

Identification

Range	cubyko
Composition	Complete installation with frame