

# RCBOs

Compact protection devices which provide MCB overload protection and RCD earth leakage protection (protect against electrical shocks by direct or indirect contacts).

	<b>Page</b>
RCBOs 1 mod, 6kA & 10kA	3
RCBOs 1 Ph/N	4
RCBOs 4 poles	6



AD110Z

**6 kA type AC - 30mA, Curve C**

Description	Pack qty.	Art No.
RCBO 1P 6kA C-6A 30mA type AC	1	<b>AD106Z</b>
RCBO 1P 6kA C-10A 30mA type AC	1	<b>AD110Z</b>
RCBO 1P 6kA C-16A 30mA type AC	1	<b>AD116Z</b>
RCBO 1P 6kA C-20A 30mA type AC	1	<b>AD120Z</b>
RCBO 1P 6kA C-32A 30mA type AC	1	<b>AD132Z</b>
RCBO 1P 6kA C-40A 30mA type AC	1	<b>AD140Z</b>



AD184

**10 kA type AC - 30mA, Curve C**

Description	Pack qty.	Art No.
RCBO 1M 1P 10kA C-6A 30mA AC	1	<b>AD184</b>
RCBO 1M 1P 10kA C-10A 30mA AC	1	<b>AD185</b>
RCBO 1M 1P 10kA C-16A 30mA AC	1	<b>AD187</b>
RCBO 1M 1P 10kA C-20A 30mA AC	1	<b>AD188</b>
RCBO 1M 1P 10kA C-25A 30mA AC	1	<b>AD189</b>
RCBO 1M 1P 10kA C-32A 30mA AC	1	<b>AD190</b>
RCBO 1M 1P 10kA C-40A 30mA AC	1	<b>AD191</b>



ADA156U

**10 kA type AC - 300mA, Curve C**

Description	Pack qty.	Art No.
RCBO 1P 10kA C-6A 30mA Type A 1M	1	<b>ADA156U</b>
RCBO 1P 10kA C-10A 30mA Type A 1M	1	<b>ADA160U</b>
RCBO 1P 10kA C-16A 30mA Type A 1M	1	<b>ADA166U</b>
RCBO 1P 10kA C-20A 30mA Type A 1M	1	<b>ADA170U</b>
RCBO 1M 1P 10kA C-25A 30mA A	1	<b>ADA175U</b>
RCBO 1P 10kA C-32A 30mA Type A 1M	1	<b>ADA182U</b>

### Curve C, 4.5kA type AC

Description	Pack qty.	Art No.
RCBO 1P+N 4.5kA C-6A 30mA AC	1	<b>AD856J</b>
RCBO 1P+N 4.5kA C-10A 30mA AC	1	<b>AD860J</b>
RCBO 1P+N 4.5kA C-16A 30mA AC	1	<b>AD866J</b>
RCBO 1P+N 4.5kA C-20A 30mA AC	1	<b>AD870J</b>
RCBO 1P+N 4.5kA C-25A 30mA AC	1	<b>AD875J</b>
RCBO 1P+N 4.5kA C-32A 30mA AC	1	<b>AD882J</b>
RCBO 1P+N 4.5kA C-40A 30mA AC	1	<b>AD890J</b>



AD856J

### Curve C, 4.5kA type A / HI

Description	Pack qty.	Art No.
RCBO 1P+N 6kA C-6A 30mA AC	1	<b>AD956B</b>
RCBO 1P+N 6kA C-10A 30mA AC	1	<b>AD960B</b>
RCBO 1P+N 6kA C-16A 30mA AC	1	<b>AD966B</b>
RCBO 1P+N 6kA C-20A 30mA AC	1	<b>AD970B</b>
RCBO 1P+N 6kA C-25A 30mA AC	1	<b>AD975B</b>
RCBO 1P+N 6kA C-32A 30mA AC	1	<b>AD982B</b>
RCBO 1P+N 6kA C-40A 30mA AC	1	<b>AD990B</b>



AD956B

### Curve C, 4,5kA type AC

Description	Pack qty.	Art No.
RCBO 1P+N 6kA C-6A 100mA AC	1	<b>AE956B</b>
RCBO 1P+N 6kA C-10A 100mA AC	1	<b>AE960B</b>
RCBO 1P+N 6kA C-16A 100mA AC	1	<b>AE966B</b>
RCBO 1P+N 6kA C-20A 100mA AC	1	<b>AE970B</b>
RCBO 1P+N 6kA C-25A 100mA AC	1	<b>AE975B</b>
RCBO 1P+N 6kA C-32A 100mA AC	1	<b>AE982B</b>
RCBO 1P+N 6kA C-40A 100mA AC	1	<b>AE990B</b>

### Curve C, 4,5kA type A / HI

Description	Pack qty.	Art No.
RCBO 1P+N 6kA C-6A 300mA AC	1	<b>AF956B</b>
RCBO 1P+N 6kA C-10A 300mA AC	1	<b>AF960B</b>
RCBO 1P+N 6kA C-16A 300mA AC	1	<b>AF966B</b>
RCBO 1P+N 6kA C-20A 300mA AC	1	<b>AF970B</b>
RCBO 1P+N 6kA C-25A 300mA AC	1	<b>AF975B</b>
RCBO 1P+N 6kA C-32A 300mA AC	1	<b>AF982B</b>
RCBO 1P+N 6kA C-40A 300mA AC	1	<b>AF990B</b>



AF990B

### Curve C, 4,5kA type A - 300mA

Description	Pack qty.	Art No.
RCBO 1P+N 6kA C-6A 300mA A	1	<b>AF956J</b>
RCBO 1P+N 6kA C-10A 300mA A	1	<b>AF960J</b>
RCBO 1P+N 6kA C-16A 300mA A	1	<b>AF966J</b>
RCBO 1P+N 6kA C-20A 300mA A	1	<b>AF970J</b>
RCBO 1P+N 6kA C-25A 300mA A	1	<b>AF975J</b>
RCBO 1P+N 6kA C-32A 300mA A	1	<b>AF982J</b>
RCBO 1P+N 6kA C-40A 300mA A	1	<b>AF990J</b>



AF956J



AD806J

**Curve B, 4,5kA type AC - 30mA**

Description	Pack qty.	Art No.
RCBO 1P+N 4.5kA B-6A 30mA AC	1	<b>AD806J</b>
RCBO 1P+N 4.5kA B-10A 30mA AC	1	<b>AD810J</b>
RCBO 1P+N 4.5kA B-16A 30mA AC	1	<b>AD816J</b>
RCBO 1P+N 4.5kA B-20A 30mA AC	1	<b>AD820J</b>
RCBO 1P+N 4.5kA B-25A 30mA AC	1	<b>AD825J</b>
RCBO 1P+N 4.5kA B-32A 30mA AC	1	<b>AD832J</b>
RCBO 1P+N 4.5kA B-40A 30mA AC	1	<b>AD840J</b>



AD906J

**Curve B, 6kA type A - 30mA**

Description	Pack qty.	Art No.
RCBO 1P+N 6kA B-6A 30mA A	1	<b>AD906J</b>
RCBO 1P+N 6kA B-10A 30mA A	1	<b>AD910J</b>
RCBO 1P+N 6kA B-16A 30mA A	1	<b>AD916J</b>
RCBO 1P+N 6kA B-20A 30mA A	1	<b>AD920J</b>
RCBO 1P+N 6kA B-25A 30mA A	1	<b>AD925J</b>
RCBO 1P+N 6kA B-32A 30mA A	1	<b>AD932J</b>
RCBO 1P+N 6kA B-40A 30mA A	1	<b>AD940J</b>



AD906B

**Curve B, 6kA type AC - 30mA**

Description	Pack qty.	Art No.
RCBO 1P+N 6kA B-6A 30mA AC	1	<b>AD906B</b>
RCBO 1P+N 6kA B-10A 30mA AC	1	<b>AD910B</b>
RCBO 1P+N 6kA B-16A 30mA AC	1	<b>AD916B</b>
RCBO 1P+N 6kA B-20A 30mA AC	1	<b>AD920B</b>
RCBO 1P+N 6kA B-25A 30mA AC	1	<b>AD925B</b>
RCBO 1P+N 6kA B-32A 30mA AC	1	<b>AD932B</b>
RCBO 1P+N 6kA B-40A 30mA AC	1	<b>AD940B</b>



AD956J

**Curve C, 6kA type A - 30mA**

Description	Pack qty.	Art No.
RCBO 1P+N 6kA C-6A 30mA A	1	<b>AD956J</b>
RCBO 1P+N 6kA C-10A 30mA A	1	<b>AD960J</b>
RCBO 1P+N 6kA C-16A 30mA A	1	<b>AD966J</b>
RCBO 1P+N 6kA C-20A 30mA A	1	<b>AD970J</b>
RCBO 1P+N 6kA C-25A 30mA A	1	<b>AD975J</b>
RCBO 1P+N 6kA C-32A 30mA A	1	<b>AD982J</b>
RCBO 1P+N 6kA C-40A 30mA A	1	<b>AD990J</b>
RCBO 1P+N 10kA C-6A 30mA A	1	<b>ADA556D</b>
RCBO 1P+N 10kA C-10A 30mA A	1	<b>ADA560D</b>
RCBO 1P+N 10kA C-16A 30mA A	1	<b>ADA566D</b>

### Curve C, 6kA type AC - 30mA

Description	Pack qty.	Art No.
RCBO 4P 6kA C-6A 30mA AC	1	<b>ADP456H</b>
RCBO 4P 6kA C-10A 30mA AC	1	<b>ADP460H</b>
RCBO 4P 6kA C-16A 30mA AC	1	<b>ADP466H</b>
RCBO 4P 6kA C-20A 30mA AC	1	<b>ADP470H</b>
RCBO 4P 6kA C-25A 30mA AC	1	<b>ADP475H</b>
RCBO 4P 6kA C-32A 30mA AC	1	<b>ADP482H</b>
RCBO 4P 6kA C-40A 30mA AC	1	<b>ADP490H</b>



ADP466H

### Curve C, 6kA type AC - 300mA

Description	Pack qty.	Art No.
RCBO 4P 6kA C-6A 300mA AC	1	<b>AFP456H</b>
RCBO 4P 6kA C-10A 300mA AC	1	<b>AFP460H</b>
RCBO 4P 6kA C-16A 300mA AC	1	<b>AFP466H</b>
RCBO 4P 6kA C-20A 300mA AC	1	<b>AFP470H</b>
RCBO 4P 6kA C-25A 300mA AC	1	<b>AFP475H</b>
RCBO 4P 6kA C-32A 300mA AC	1	<b>AFP482H</b>
RCBO 4P 6kA C-40A 300mA AC	1	<b>AFP490H</b>



ADP466H

### Curve C, 10kA type AC - 30mA

Description	Pack qty.	Art No.
RCBO 4P 10kA C-6A 30mA type AC	1	<b>ADQ456H</b>
RCBO 4P 10kA C-10A 30mA type AC	1	<b>ADQ460H</b>
RCBO 4P 10kA C-16A 30mA type AC	1	<b>ADQ466H</b>
RCBO 4P 10kA C-20A 30mA type AC	1	<b>ADQ470H</b>
RCBO 4P 10kA C-25A 30mA type AC	1	<b>ADQ475H</b>
RCBO 4P 10kA C-32A 30mA type AC	1	<b>ADQ482H</b>
RCBO 4P 10kA C-40A 30mA type AC	1	<b>ADQ490H</b>



ADQ456H

### Curve C, 10kA type AC - 300mA

Description	Pack qty.	Art No.
RCBO 4P 10kA C-6A 300mA type AC	1	<b>AFQ456H</b>
RCBO 4P 10kA C-10A 300mA type AC	1	<b>AFQ460H</b>
RCBO 4P 10kA C-16A 300mA type AC	1	<b>AFQ466H</b>
RCBO 4P 10kA C-20A 300mA type AC	1	<b>AFQ470H</b>
RCBO 4P 10kA C-25A 300mA type AC	1	<b>AFQ475H</b>
RCBO 4P 10kA C-32A 300mA type AC	1	<b>AFQ482H</b>
RCBO 4P 10kA C-40A 300mA type AC	1	<b>AFQ490H</b>



AFQ460H