



CD280F

2 pole type AC


Description	Pack qty.	Art No.
RCCB 2P 25A 10mA AC	1	CCC225F
RCCB 2P 80A 30mA AC	1	CD280F
RCCB 2P 25A 30mA AC	1	CDC225F
RCCB 2P 40A 30mA AC	1	CDC240F
RCCB 2P 63A 30mA AC	1	CDC263F
RCCB 2P 40A 100mA AC	1	CEC240F
RCCB 2P 63A 100mA AC	1	CEC263F
RCCB 2P 80A 300mA AC	1	CF280F
RCCB 2P 25A 300mA AC	1	CFC225F
RCCB 2P 40A 300mA AC	1	CFC240F
RCCB 2P 63A 300mA AC	1	CFC263F
RCCB 2P 25A 500mA AC	1	CGC225F
RCCB 2P 40A 500mA AC	1	CGC240F
RCCB 2P 63A 500mA AC	1	CGC263F
RCCB 2P 63A 300mA AC S	1	CPC263F



CDC425F

4 pole type AC

Description	Pack qty.	Art No.
RCCB 4P 25A 30mA AC	1	CDC425F
RCCB 4P 40A 30mA AC	1	CDC440F
RCCB 4P 63A 30mA AC	1	CDC463F
RCCB 4P 40A 100mA AC	1	CEC440F
RCCB 4P 63A 100mA AC	1	CEC463F
RCCB 4P 80A 300mA AC	1	CF480F
RCCB 4P 100A 300mA AC	1	CF485F
RCCB 4P 25A 300mA AC	1	CFC425F
RCCB 4P 40A 300mA AC	1	CFC440F
RCCB 4P 63A 300mA AC	1	CFC463F
RCCB 4P 25A 500mA AC	1	CGC425F
RCCB 4P 40A 500mA AC	1	CGC440F
RCCB 4P 63A 500mA AC	1	CGC463F
RCCB 4P 80A 300mA AC S	1	CP480F
RCCB 4P 100A 300mA AC S	1	CP485F
RCCB 4P 40A 300mA AC S	1	CPC440F
RCCB 4P 63A 300mA AC S	1	CPC463F
RCCB 4P 125A 300mA AC	1	CFC490F



CDH225F

2 pole type A / HI

Description	Pack qty.	Art No.
RCCB 2P 25A 30mA HI	1	CDH225F
RCCB 2P 40A 30mA HI	1	CDH240F
RCCB 2P 63A 30mA HI	1	CDH263F
RCCB 2P 25A 300mA HI	1	CFH225F
RCCB 2P 40A 300mA HI	1	CFH240F
RCCB 2P 63A 300mA HI	1	CFH263F



CDJ225S

4 pole type A / HI

Description	Pack qty.	Art No.
RCCB 4P 25A 30mA HI	1	CDH425F
RCCB 4P 40A 30mA HI	1	CDH440F
RCCB 4P 63A 30mA HI	1	CDH463F
RCCB 4P 25A 300mA HI	1	CFH425F
RCCB 4P 40A 300mA HI	1	CFH440F
RCCB 4P 63A 300mA HI	1	CFH463F

Accessories

Description	Pack qty.	Art No.
Contact for RCCB 2(1C+1O) 6A 240V AC	1	CZ001
Sealable terminal covers RCCB 25/63A 2M	10	CZN005
Sealable terminal covers RCCB 25/63A 4M	1	CZN006



CZ001