



HLE180S

## 1 pole, Curve B, 10 000 A / 10 kA

Description	Pack qty.	Art No.
MCB 1P 10kA B-80A 1.5M	1	<b>HLE180S</b>
MCB 1P 10kA B-100A 1.5M	1	<b>HLE190S</b>
MCB 1P 10kA B-125A 1.5M	1	<b>HLE199S</b>



HLE280S

## 2 pole, Curve B, 10 000 A / 10 kA

Description	Pack qty.	Art No.
MCB 2P 10kA B-80A 3M	1	<b>HLE280S</b>
MCB 2P 10kA B-100A 3M	1	<b>HLE290S</b>
MCB 2P 10kA B-125A 3M	1	<b>HLE299S</b>



HLE380S

## 3 pole, Curve B, 10 000 A / 10 kA

Description	Pack qty.	Art No.
MCB 3P 10kA B-80A 4.5M	1	<b>HLE380S</b>
MCB 3P 10kA B-100A 4.5M	1	<b>HLE390S</b>
MCB 3P 10kA B-125A 4.5M	1	<b>HLE399S</b>



HLE480S

## 4 pole, Curve B, 10 000 A / 10 kA

Description	Pack qty.	Art No.
MCB 4P 10kA B-80A 6M	1	<b>HLE480S</b>
MCB 4P 10kA B-100A 6M	1	<b>HLE490S</b>
MCB 4P 10kA B-125A 6M	1	<b>HLE499S</b>



HLF180S

## 1 pole, Curve C, 10 000 A / 10 kA

Description	Pack qty.	Art No.
MCB 1P 10kA C-80A 1.5M	1	<b>HLF180S</b>
MCB 1P 10kA C-100A 1.5M	1	<b>HLF190S</b>
MCB 1P 10kA C-125A 1.5M	1	<b>HLF199S</b>

## 2 pole, Curve C, 10 000 A / 10 kA

Description	Pack qty.	Art No.
MCB 2P 10kA C-80A 3M	1	<b>HLF280S</b>
MCB 2P 10kA C-100A 3M	1	<b>HLF290S</b>
MCB 2P 10kA C-125A 3M	1	<b>HLF299S</b>



HLF280S

## 3 pole, Curve C, 10 000 A / 10 kA


Description	Pack qty.	Art No.
MCB 3P 10kA C-80A 4.5M	1	<b>HLF380S</b>
MCB 3P 10kA C-100A 4.5M	1	<b>HLF390S</b>
MCB 3P 10kA C-125A 4.5M	1	<b>HLF399S</b>



HLF380S

## 4 pole, Curve C, 10 000 A / 10 kA

Description	Pack qty.	Art No.
MCB 4P 10kA C-80A 6M	1	<b>HLF480S</b>
MCB 4P 10kA C-100A 6M	1	<b>HLF490S</b>
MCB 4P 10kA C-125A 6M	1	<b>HLF499S</b>



HLF480S

## 1 pole, Curve B, 15 000 A / 15 kA

Description	Pack qty.	Art No.
MCB 1P 15kA B-80A 1.5M	1	<b>HMB180</b>
MCB 1P 15kA B-100A 1.5M	1	<b>HMB190</b>
MCB 1P 15kA B-125A 1.5M	1	<b>HMB199</b>



HMB180

## 2 pole, Curve B, 15 000 A / 15 kA

Description	Pack qty.	Art No.
MCB 2P 15kA B-80A 3M	1	<b>HMB280</b>
MCB 2P 15kA B-100A 3M	1	<b>HMB290</b>
MCB 2P 15kA B-125A 3M	1	<b>HMB299</b>




HMB280



### 3 pole, Curve B, 15 000 A / 15 kA

Description	Pack qty.	Art No.
MCB 3P 15kA B-80A 4.5M	1	<b>HMB380</b>
MCB 3P 15kA B-100A 4.5M	1	<b>HMB390</b>
MCB 3P 15kA B-125A 4.5M	1	<b>HMB399</b>

HMB380



### 4 pole, Curve B, 15 000 A / 15 kA

Description	Pack qty.	Art No.
MCB 4P 15kA B-80A 6M	1	<b>HMB480</b>
MCB 4P 15kA B-100A 6M	1	<b>HMB490</b>
MCB 4P 15kA B-125A 6M	1	<b>HMB499</b>

HMB480



### 1 pole, Curve C, 15 000 A / 15 kA

Description	Pack qty.	Art No.
MCB 1P 15kA C-80A 1.5M	1	<b>HMC180</b>
MCB 1P 15kA C-100A 1.5M	1	<b>HMC190</b>
MCB 1P 15kA C-125A 1.5M	1	<b>HMC199</b>

HMC180



### 2 pole, Curve C, 15 000 A / 15 kA

Description	Pack qty.	Art No.
MCB 2P 15kA C-80A 3M	1	<b>HMC280</b>
MCB 2P 15kA C-100A 3M	1	<b>HMC290</b>
MCB 2P 15kA C-125A 3M	1	<b>HMC299</b>

HMC280




### 3 pole, Curve C, 15 000 A / 15 kA

Description	Pack qty.	Art No.
MCB 3P 15kA C-80A 4.5M	1	<b>HMC380</b>
MCB 3P 15kA C-100A 4.5M	1	<b>HMC390</b>
MCB 3P 15kA C-125A 4.5M	1	<b>HMC399</b>

HMC380

## 4 pole, Curve C, 15 000 A / 15 kA

Description	Pack qty.	Art No.
MCB 4P 15kA C-80A 6M	1	<b>HMC480</b>
MCB 4P 15kA C-100A 6M	1	<b>HMC490</b>
MCB 4P 15kA C-125A 6M	1	<b>HMC499</b>



HMC480

## 1 pole, Curve D, 15 000 A / 15 kA


Description	Pack qty.	Art No.
MCB 1P 15kA D-80A 1.5M	1	<b>HMD180</b>
MCB 1P 15kA D-100A 1.5M	1	<b>HMD190</b>
MCB 1P 15kA D-125A 1.5M	1	<b>HMD199</b>



HMD180

## 2 pole, Curve D, 15 000 A / 15 kA


Description	Pack qty.	Art No.
MCB 2P 15kA D-80A 3M	1	<b>HMD280</b>
MCB 2P 15kA D-100A 3M	1	<b>HMD290</b>
MCB 2P 15kA D-125A 3M	1	<b>HMD299</b>



HMD280

## 3 pole, Curve D, 15 000 A / 15 kA


Description	Pack qty.	Art No.
MCB 3P 15kA D-80A 4.5M	1	<b>HMD380</b>
MCB 3P 15kA D-100A 4.5M	1	<b>HMD390</b>
MCB 3P 15kA D-125A 4.5M	1	<b>HMD399</b>



HMD380

## 4 pole, Curve D, 15 000 A / 15 kA

Description	Pack qty.	Art No.
MCB 4P 15kA D-80A 6M	1	<b>HMD480</b>
MCB 4P 15kA D-100A 6M	1	<b>HMD490</b>
MCB 4P 15kA D-125A 6M	1	<b>HMD499</b>



HMD480



HMK180

## 1 pole, Curve C, 30 kA


Description	Pack qty.	Art No.
MCB 1P 30kA C-80A 1.5M	1	<b>HMK180</b>
MCB 1P 30kA C-100A 1.5M	1	<b>HMK190</b>
MCB 1P 30kA C-125A 1.5M	1	<b>HMK199</b>



HMK280

## 2 pole, Curve C, 30 kA


Description	Pack qty.	Art No.
MCB 2P 30kA C-80A 3M	1	<b>HMK280</b>
MCB 2P 30kA C-100A 3M	1	<b>HMK290</b>
MCB 2P 30kA C-125A 3M	1	<b>HMK299</b>



HMK380

## 3 pole, Curve C, 30 kA

Description	Pack qty.	Art No.
MCB 3P 30kA C-80A 4.5M	1	<b>HMK380</b>
MCB 3P 30kA C-100A 4.5M	1	<b>HMK390</b>
MCB 3P 30kA C-125A 4.5M	1	<b>HMK399</b>



HMK480

## 4 pole, Curve C, 30 kA

Description	Pack qty.	Art No.
MCB 4P 30kA C-80A 6M	1	<b>HMK480</b>
MCB 4P 30kA C-100A 6M	1	<b>HMK490</b>
MCB 4P 30kA C-125A 6M	1	<b>HMK499</b>



HMX110

## 1 pole, Curve C, 50 kA

Description	Pack qty.	Art No.
MCB 1P 50kA C-10A 1.5M	1	<b>HMX110</b>
MCB 1P 50kA C-16A 1.5M	1	<b>HMX116</b>
MCB 1P 50kA C-20A 1.5M	1	<b>HMX120</b>
MCB 1P 50kA C-25A 1.5M	1	<b>HMX125</b>
MCB 1P 50kA C-32A 1.5M	1	<b>HMX132</b>
MCB 1P 50kA C-40A 1.5M	1	<b>HMX140</b>
MCB 1P 50kA C-50A 1.5M	1	<b>HMX150</b>
MCB 1P 50kA C-63A 1.5M	1	<b>HMX163</b>

## 2 pole, Curve C, 50 kA

Description	Pack qty.	Art No.
MCB 2P 50kA C-10A 3M	1	<b>HMX210</b>
MCB 2P 50kA C-16A 3M	1	<b>HMX216</b>
MCB 2P 50kA C-20A 3M	1	<b>HMX220</b>
MCB 2P 50kA C-25A 3M	1	<b>HMX225</b>
MCB 2P 50kA C-32A 3M	1	<b>HMX232</b>
MCB 2P 50kA C-40A 3M	1	<b>HMX240</b>
MCB 2P 50kA C-50A 3M	1	<b>HMX250</b>
MCB 2P 50kA C-63A 3M	1	<b>HMX263</b>



HMX210

## 3 pole, Curve C, 50 kA


Description	Pack qty.	Art No.
MCB 3P 50kA C-10A 4.5M	1	<b>HMX310</b>
MCB 3P 50kA C-16A 4.5M	1	<b>HMX316</b>
MCB 3P 50kA C-20A 4.5M	1	<b>HMX320</b>
MCB 3P 50kA C-25A 4.5M	1	<b>HMX325</b>
MCB 3P 50kA C-32A 4.5M	1	<b>HMX332</b>
MCB 3P 50kA C-40A 4.5M	1	<b>HMX340</b>
MCB 3P 50kA C-50A 4.5M	1	<b>HMX350</b>
MCB 3P 50kA C-63A 4.5M	1	<b>HMX363</b>



HMX310

## 4 pole, Curve C, 50 kA

Description	Pack qty.	Art No.
MCB 4P 50kA C-10A 6M	1	<b>HMX410</b>
MCB 4P 50kA C-16A 6M	1	<b>HMX416</b>
MCB 4P 50kA C-20A 6M	1	<b>HMX420</b>
MCB 4P 50kA C-25A 6M	1	<b>HMX425</b>
MCB 4P 50kA C-32A 6M	1	<b>HMX432</b>
MCB 4P 50kA C-40A 6M	1	<b>HMX440</b>
MCB 4P 50kA C-50A 6M	1	<b>HMX450</b>
MCB 4P 50kA C-63A 6M	1	<b>HMX463</b>



HMX410

## Cover and separator

Description	Pack qty.	Art No.
Terminal cover 1P	4	<b>MZN130</b>
1 set of 3 interpole barriers	1	<b>MZN131</b>



MZN130