

RCBOs

	Page
1 Ph/N RCBOs	3
4 pole RCBOs	5



ACC816F

Curve C, 4500 A / 6 kA type AC

Description	Pack qty.	Art No.
RCBO 1P+N 4.5/6kA C-16A 10mA AC	1	ACC816F
RCBO 1P+N 4.5kA C-2A 30mA AC	1	ADC802F
RCBO 1P+N 4.5kA C-6A 30mA AC	1	ADC806F
RCBO 1P+N 4.5kA C-10A 30mA AC	1	ADC810F
RCBO 1P+N 4.5kA C-16A 30mA AC	1	ADC816F
RCBO 1P+N 4.5kA C-20A 30mA AC	1	ADC820F
RCBO 1P+N 4.5kA C-25A 30mA AC	1	ADC825F
RCBO 1P+N 4.5kA C-32A 30mA AC	1	ADC832F
RCBO 1P+N 4.5kA C-40A 30mA AC	1	ADC840F
RCBO 1P+N 4.5kA C-6A 300mA AC	1	AFC806F
RCBO 1P+N 4.5kA C-10A 300mA AC	1	AFC810F
RCBO 1P+N 4.5kA C-16A 300mA AC	1	AFC816F
RCBO 1P+N 4.5kA C-20A 300mA AC	1	AFC820F
RCBO 1P+N 4.5kA C-25A 300mA AC	1	AFC825F
RCBO 1P+N 4.5kA C-32A 300mA AC	1	AFC832F
RCBO 1P+N 4.5kA C-40A 300mA AC	1	AFC840F



ADC816F

Curve C, 4500 A / 6 kA type A / HI

Description	Pack qty.	Art No.
RCBO 1P+N 4.5kA C-10A 30mA HI	1	ADH810F
RCBO 1P+N 4.5kA C-16A 30mA HI	1	ADH816F
RCBO 1P+N 4.5kA C-20A 30mA HI	1	ADH820F
RCBO 1P+N 4.5kA C-25A 30mA HI	1	ADH825F
RCBO 1P+N 4.5kA C-32A 30mA HI	1	ADH832F
RCBO.1P+N 4.5kA C-10A 300mA HI	1	AFH810F
RCBO.1P+N 4.5kA C-16A 300mA HI	1	AFH816F
RCBO.1P+N 4.5kA C-20A 300mA HI	1	AFH820F



ADC816F

Curve C, 6000 A / 10 kA type AC

Description	Pack qty.	Art No.
RCBO 1P+N 6kA C-6A 30mA AC	1	ADC906F
RCBO 1P+N 6kA C-10A 30mA AC	1	ADC910F
RCBO 1P+N 6kA C-16A 30mA AC	1	ADC916F
RCBO 1P+N 6kA C-20A 30mA AC	1	ADC920F
RCBO 1P+N 6kA C-25A 30mA AC	1	ADC925F
RCBO 1P+N 6kA C-32A 30mA AC	1	ADC932F
RCBO 1P+N 6kA C-40A 30mA AC	1	ADC940F
RCBO 1P+N 6kA C-6A 300mA AC	1	AFC906F
RCBO 1P+N 6kA C-10A 300mA AC	1	AFC910F
RCBO 1P+N 6kA C-16A 300mA AC	1	AFC916F
RCBO 1P+N 6kA C-20A 300mA AC	1	AFC920F
RCBO 1P+N 6kA C-25A 300mA AC	1	AFC925F
RCBO 1P+N 6kA C-32A 300mA AC	1	AFC932F
RCBO 1P+N 6kA C-40A 300mA AC	1	AFC940F
RCBO 1P+N 6kA C-16A 10mA AC	1	ACC916F



ADC816F

Curve C, 6000 A / 10 kA type A / HI

Description	Pack qty.	Art No.
RCBO 1P+N 6kA C-6A 30mA HI	1	ADH906F
RCBO 1P+N 6kA C-10A 30mA HI	1	ADH910F
RCBO 1P+N 6kA C-16A 30mA HI	1	ADH916F
RCBO 1P+N 6kA C-20A 30mA HI	1	ADH920F
RCBO 1P+N 6kA C-25A 30mA HI	1	ADH925F
RCBO 1P+N 6kA C-40A 30mA HI	1	ADH940F
RCBO 1P+N 6kA C-10A 300mA HI	1	AFH910F
RCBO 1P+N 6kA C-16A 300mA HI	1	AFH916F
RCBO 1P+N 6kA C-20A 300mA HI	1	AFH920F
RCBO 1P+N 6kA C-25A 300mA HI	1	AFH925F
RCBO 1P+N 6kA C-32A 300mA HI	1	AFH932F
RCBO 1P+N 6kA C-40A 300mA HI	1	AFH940F

Terminal covers

Description	Pack qty.	Art No.
Yellow terminal covers sealable RCBO 2M	4	AZ010
1 set of 2 grey terminal covers RCBO 2M	4	AZ002



AZ010



ADM406G

Curve B

Description	Pack qty.	Art No.
RCBO 4P 6kA B-6A 30mA A	1	ADM406G
RCBO 4P 6kA B-10A 30mA A	1	ADM410G
RCBO 4P 6kA B-16A 30mA A	1	ADM416G
RCBO 4P 6kA B-20A 30mA A	1	ADM420G
RCBO 4P 6kA B-25A 30mA A	1	ADM425G
RCBO 4P 6kA B-32A 30mA A	1	ADM432G
RCBO 4P 6kA B-40A 30mA A	1	ADM440G



ADC410F

Type AC curve C

Description	Pack qty.	Art No.
RCBO 3P+N 6/10kA C-10A 30mA AC	1	ADC410F
RCBO 3P+N 6/10kA C-16A 30mA AC	1	ADC416F
RCBO 3P+N 6/10kA C-20A 30mA AC	1	ADC420F
RCBO 3P+N 6/10kA C-32A 30mA AC	1	ADC432F
RCBO 3P+N 6/10kA C-16A 300mA AC	1	AFC416F
RCBO 3P+N 6/10kA C-20A 300mA AC	1	AFC420F