

# RCCBs

	<b>Page</b>
RCCBs type AC or A / HI	3
RCCBs type B NL	5
RCCBs type B	6
RCCBs type A and accessories	7



CD280F

## 2 pole type AC


Description	Pack qty.	Art No.
RCCB 2P 25A 10mA AC	1	CCC225F
RCCB 2P 80A 30mA AC	1	CD280F
RCCB 2P 25A 30mA AC	1	CDC225F
RCCB 2P 40A 30mA AC	1	CDC240F
RCCB 2P 63A 30mA AC	1	CDC263F
RCCB 2P 40A 100mA AC	1	CEC240F
RCCB 2P 63A 100mA AC	1	CEC263F
RCCB 2P 80A 300mA AC	1	CF280F
RCCB 2P 25A 300mA AC	1	CFC225F
RCCB 2P 40A 300mA AC	1	CFC240F
RCCB 2P 63A 300mA AC	1	CFC263F
RCCB 2P 25A 500mA AC	1	CGC225F
RCCB 2P 40A 500mA AC	1	CGC240F
RCCB 2P 63A 500mA AC	1	CGC263F
RCCB 2P 63A 300mA AC S	1	CPC263F



CDC425F

## 4 pole type AC

Description	Pack qty.	Art No.
RCCB 4P 25A 30mA AC	1	CDC425F
RCCB 4P 40A 30mA AC	1	CDC440F
RCCB 4P 63A 30mA AC	1	CDC463F
RCCB 4P 40A 100mA AC	1	CEC440F
RCCB 4P 63A 100mA AC	1	CEC463F
RCCB 4P 80A 300mA AC	1	CF480F
RCCB 4P 100A 300mA AC	1	CF485F
RCCB 4P 25A 300mA AC	1	CFC425F
RCCB 4P 40A 300mA AC	1	CFC440F
RCCB 4P 63A 300mA AC	1	CFC463F
RCCB 4P 25A 500mA AC	1	CGC425F
RCCB 4P 40A 500mA AC	1	CGC440F
RCCB 4P 63A 500mA AC	1	CGC463F
RCCB 4P 80A 300mA AC S	1	CP480F
RCCB 4P 100A 300mA AC S	1	CP485F
RCCB 4P 40A 300mA AC S	1	CPC440F
RCCB 4P 63A 300mA AC S	1	CPC463F
RCCB 4P 125A 300mA AC	1	CFC490F



CDH225F

## 2 pole type A / HI

Description	Pack qty.	Art No.
RCCB 2P 25A 30mA HI	1	CDH225F
RCCB 2P 40A 30mA HI	1	CDH240F
RCCB 2P 63A 30mA HI	1	CDH263F
RCCB 2P 25A 300mA HI	1	CFH225F
RCCB 2P 40A 300mA HI	1	CFH240F
RCCB 2P 63A 300mA HI	1	CFH263F



CDJ225S

## 4 pole type A / HI

Description	Pack qty.	Art No.
RCCB 4P 25A 30mA HI	1	CDH425F
RCCB 4P 40A 30mA HI	1	CDH440F
RCCB 4P 63A 30mA HI	1	CDH463F
RCCB 4P 25A 300mA HI	1	CFH425F
RCCB 4P 40A 300mA HI	1	CFH440F
RCCB 4P 63A 300mA HI	1	CFH463F

**Accessories**

Description	Pack qty.	Art No.
Contact for RCCB 2(1C+10) 6A 240V AC	1	<b>CZ001</b>
Sealable terminal covers RCCB 25/63A 2M	10	<b>CZN005</b>
Sealable terminal covers RCCB 25/63A 4M	1	<b>CZN006</b>



CZ001



CDB125F

### 1P+N 30mA

Description	Pack qty.	Art No.
RCCB 1P+N 25A 30mA B	1	<b>CDB125F</b>
RCCB 1P+N 40A 30mA B	1	<b>CDB140F</b>
RCCB 1P+N 63A 30mA B	1	<b>CDB163F</b>



CFB125F

### 1P+N 30mA

Description	Pack qty.	Art No.
RCCB 1P+N 25A 300mA B	1	<b>CFB125F</b>
RCCB 1P+N 40A 300mA B	1	<b>CFB140F</b>
RCCB 1P+N 63A 300mA B	1	<b>CFB163F</b>



CDB725F

### 3P+N 30mA

Description	Pack qty.	Art No.
RCCB 3P+N 25A 30mA B	1	<b>CDB725F</b>
RCCB 3P+N 40A 30mA B	1	<b>CDB740F</b>
RCCB 3P+N 63A 30mA B	1	<b>CDB763F</b>



CFB725F

### 3P+N 300mA

Description	Pack qty.	Art No.
RCCB 3P+N 25A 300mA B	1	<b>CFB725F</b>
RCCB 3P+N 40A 300mA B	1	<b>CFB740F</b>
RCCB 3P+N 63A 300mA B	1	<b>CFB763F</b>

**4 pole type B**

Description	Pack qty.	Art No.
RCCB 4P 63A 30mA B	1	<b>CDB463F</b>
RCCB 4P 40A 300mA B	1	<b>CFB440F</b>
RCCB 4P 63A 300mA B	1	<b>CFB463F</b>



CDB463F



CDA263S

## RCCBs type A and accessories

Description	Pack qty.	Art No.
RCCB auto reclosing 2P 63A 30mA A 4M	1	<b>CDA263S</b>