

Cartouches-fusibles



LF300G

Type gG

| Description | Pack qty. | Art No. |
|--------------------------------------|-----------|---------|
| Fusibles cylindrique 10x38mm gG 0.5A | 10 | LF300G |
| Fusibles cylindrique 10x38mm gG 1A | 10 | LF301G |
| Fusibles cylindrique 10x38mm gG 2A | 10 | LF302G |
| Fusibles cylindrique 10x38mm gG 4A | 10 | LF304G |
| Fusibles cylindrique 10x38mm gG 6A | 10 | LF306G |
| Fusibles cylindrique 10x38mm gG 8A | 10 | LF308G |
| Fusibles cylindrique 10x38mm gG 10A | 10 | LF310G |
| Fusibles cylindrique 10x38mm gG 12A | 10 | LF312G |
| Fusibles cylindrique 10x38mm gG 16A | 10 | LF316G |
| Fusibles cylindrique 10x38mm gG 20A | 10 | LF320G |
| Fusibles cylindrique 10x38mm gG 25A | 10 | LF325G |
| Fusibles cylindrique 10x38mm gG 32A | 10 | LF332G |
| Cartouche fus.14x51 gG 2A | 10 | LF402G |
| Cartouche fus.14x51 gG 4A | 10 | LF404G |
| Cartouche fus.14x51 gG 6A | 10 | LF406G |
| Cartouche fus.14x51 gG 8A | 10 | LF408G |
| Cartouche fus.14x51 gG 10A | 10 | LF410G |
| Cartouche fus.14x51 gG 12A | 10 | LF412G |
| Cartouche fus.14x51 gG 16A | 10 | LF416G |
| Cartouche fus.14x51 gG 20A | 10 | LF420G |
| Cartouche fus.14x51 gG 25A | 10 | LF425G |
| Cartouche fus.14x51 gG 32A | 10 | LF432G |
| Cartouche fus.14x51 gG 40A | 10 | LF440G |
| Cartouche-fusible indus 14x51 gG 45A | 10 | LF445G |
| Cartouche fus.14x51 gG 50A | 10 | LF450G |
| Fusibles cylindrique 22x58mm gG 16A | 10 | LF516G |
| Fusibles cylindrique 22x58mm gG 20A | 10 | LF520G |
| Fusibles cylindrique 22x58mm gG 25A | 10 | LF525G |
| Fusibles cylindrique 22x58mm gG 32A | 10 | LF532G |
| Fusibles cylindrique 22x58mm gG 40A | 10 | LF540G |
| Fusibles cylindrique 22x58mm gG 50A | 10 | LF550G |
| Fusibles cylindrique 22x58mm gG 63A | 10 | LF563G |
| Fusibles cylindrique 22x58mm gG 80A | 10 | LF580G |
| Fusibles cylindrique 22x58mm gG 100A | 10 | LF590G |
| Fusibles cylindrique 22x58mm gG 125A | 10 | LF599G |

Type aM

| Description | Pack qty. | Art No. |
|--------------------------------------|-----------|---------------|
| Fusibles cylindrique 10x38mm aM 0.5A | 10 | LF300M |
| Fusibles cylindrique 10x38mm aM 1A | 10 | LF301M |
| Fusibles cylindrique 10x38mm aM 2A | 10 | LF302M |
| Fusibles cylindrique 10x38mm aM 4A | 10 | LF304M |
| Fusibles cylindrique 10x38mm aM 6A | 10 | LF306M |
| Fusibles cylindrique 10x38mm aM 8A | 10 | LF308M |
| Fusibles cylindrique 10x38mm aM 10A | 10 | LF310M |
| Fusibles cylindrique 10x38mm aM 12A | 10 | LF312M |
| Fusibles cylindrique 10x38mm aM 16A | 10 | LF316M |
| Fusibles cylindrique 10x38mm aM 20A | 10 | LF320M |
| Fusibles cylindrique 10x38mm aM 25A | 10 | LF325M |
| Fusibles cylindrique 10x38mm aM 32A | 10 | LF332M |
| Cartouche fus.14x51 aM 2A | 10 | LF402M |
| Cartouche fus.14x51 aM 4A | 10 | LF404M |
| Cartouche fus.14x51 aM 6A | 10 | LF406M |
| Cartouche fus.14x51 aM 8A | 10 | LF408M |
| Cartouche fus.14x51 aM 10A | 10 | LF410M |
| Cartouche fus.14x51 aM 12A | 10 | LF412M |
| Cartouche fus.14x51 aM 16A | 10 | LF416M |
| Cartouche fus.14x51 aM 20A | 10 | LF420M |
| Cartouche fus.14x51 aM 25A | 10 | LF425M |
| Cartouche fus.14x51 aM 32A | 10 | LF432M |
| Cartouche fus.14x51 aM 40A | 10 | LF440M |
| Cartouche-fusible indus 14x51 aM 45A | 10 | LF445M |
| Cartouche fus.14x51 aM 50A | 10 | LF450M |
| Fusibles cylindrique 22x58mm aM 16A | 10 | LF516M |
| Fusibles cylindrique 22x58mm aM 20A | 10 | LF520M |
| Fusibles cylindrique 22x58mm aM 25A | 10 | LF525M |
| Fusibles cylindrique 22x58mm aM 32A | 10 | LF532M |
| Fusibles cylindrique 22x58mm aM 40A | 10 | LF540M |
| Fusibles cylindrique 22x58mm aM 50A | 10 | LF550M |
| Fusibles cylindrique 22x58mm aM 63A | 10 | LF563M |
| Fusibles cylindrique 22x58mm aM 80A | 10 | LF580M |
| Fusibles cylindrique 22x58mm aM 100A | 10 | LF590M |
| Fusibles cylindrique 22x58mm aM 125A | 10 | LF599M |



LF300M