



HHB100Z

## MCCBs h250 3 pole 25 kA

Description	Pack qty.	Art No.
MCCB X250 3P 25kA 100A TM	1	<b>HHB100Z</b>
MCCB X250 3P 25kA 125A TM	1	<b>HHB125Z</b>
MCCB X250 3P 25kA 160A TM	1	<b>HHB160Z</b>
MCCB X250 3P 25kA 200A TM	1	<b>HHB200Z</b>
MCCB X250 3P 25kA 250A TM	1	<b>HHB250Z</b>

## MCCBs h250 4 pole 25 kA

Description	Pack qty.	Art No.
MCCB X250 4P 25kA 160A TM	1	<b>HHB161Z</b>
MCCB X250 4P 25kA 200A TM	1	<b>HHB201Z</b>
MCCB X250 4P 25kA 250A TM	1	<b>HHB251Z</b>



HNB100H

## MCCBs x250 3 pole 40 kA

Description	Pack qty.	Art No.
MCCB X250 3P 40kA 100A TM	1	<b>HNB100H</b>
MCCB X250 3P 40kA 125A TM	1	<b>HNB125H</b>
MCCB X250 3P 40kA 160A TM	1	<b>HNB160H</b>
MCCB X250 3P 40kA 200A TM	1	<b>HNB200H</b>
MCCB X250 3P 40kA 250A TM	1	<b>HNB250H</b>
MCCB x250 3P 40kA 160A TM	1	<b>HNB160Z</b>
MCCB x250 3P 40kA 250A TM	1	<b>HNB250Z</b>



HNB101H

## MCCBs h250 4 pole 40 kA

Description	Pack qty.	Art No.
MCCB X250 4P 40kA 100A TM	1	<b>HNB101H</b>
MCCB X250 4P 60% 40kA 100A TM	1	<b>HNB102H</b>
MCCB X250 4P 40kA 125A TM	1	<b>HNB126H</b>
MCCB X250 4P 60% 40kA 125A TM	1	<b>HNB127H</b>
MCCB X250 4P 40kA 160A TM	1	<b>HNB161H</b>
MCCB X250 4P 60% 40kA 160A TM	1	<b>HNB162H</b>
MCCB X250 4P 40kA 200A TM	1	<b>HNB201H</b>
MCCB X250 4P 60% 40kA 200A TM	1	<b>HNB202H</b>
MCCB X250 4P 40kA 250A TM	1	<b>HNB251H</b>
MCCB X250 4P 60% 40kA 250A TM	1	<b>HNB252H</b>
MCCB x250 4P 40kA 125A TM	1	<b>HNB126Z</b>
MCCB x250 4P 40kA 160A TM	1	<b>HNB161Z</b>



HCB250H

## Trip-free switches x250 3 pole

Description	Pack qty.	Art No.
Switch X250 3P 250A	1	<b>HCB250H</b>

**Trip-free switches x250 4 pole**

Description	Pack qty.	Art No.
Switch X250 4P 250A	1	<b>HCB251H</b>



HCB251H

**Settable add-on-blocks x250**

Description	Pack qty.	Art No.
RCD add on x250 4P 160A ldn adj	1	<b>HBB161H</b>
RCD add on x250 4P 250A ldn adj	1	<b>HBB251H</b>



HBB161H

**Auxiliary contacts**

Description	Pack qty.	Art No.
AX contact 1NO+NC 250VAC (x/P160...x/P630)	1	<b>HXA021H</b>
AL contact 1NO+NC 250VAC (x/P160...x/P630)	1	<b>HXA024H</b>
AX low lvl. 1NO+NC 125VAC(x/P160...x/P630)	1	<b>HXA025H</b>
AL low lvl. 1NO+NC 125VAC(x/P160...x/P630)	1	<b>HXA026H</b>



HXA021H

**Shunt trip**

Description	Pack qty.	Art No.
Shunt trip 24V DC (x/P160-x/P250-x/P630)	1	<b>HXA001H</b>
Shunt trip 48V DC (x/P160-x/P250-x/P630)	1	<b>HXA002H</b>
SHT 100-120V AC (x/P160-x/P250-x/P630)	1	<b>HXA003H</b>
SHT 200-240V AC (x/P160-x/P250-x/P630)	1	<b>HXA004H</b>
SHT 380-450V AC (x/P160-x/P250-x/P630)	1	<b>HXA005H</b>



HXA001H

**Undervoltage release**

Description	Pack qty.	Art No.
UVR 24V DC (x/P160-x/P250-x/P630)	1	<b>HXA011H</b>
UVR 100-120V AC (x/P160-x/P250-x/P630)	1	<b>HXA013H</b>
UVR 200-240V AC (x/P160-x/P250-x/P630)	1	<b>HXA014H</b>



HXA011H



**UVR delayed**

Description	Pack qty.	Art No.
UVR delayed 24V DC (x/P160-P160-x250-P250)	1	<b>HXA051H</b>
UVR delayed 110-120VAC (x/P 160-x/P 250)	1	<b>HXA053H</b>
UVR delayed 220-240VAC (x/P 160-x/P 250)	1	<b>HXA054H</b>
UVR delayed 380-450V AC (x/P160-x/P250)	1	<b>HXA055H</b>

HXA051H



**Direct rotary handle**

Description	Pack qty.	Art No.
Direct rotary handle x250	1	<b>HXB030H</b>

HXB030H



**Extended rotary handle**

Description	Pack qty.	Art No.
Extended rotary handle x250	1	<b>HXB031H</b>

HXB031H



**Locking kit**

Description	Pack qty.	Art No.
Padlock (x160-P160-x250-P250-x630)	1	<b>HXA039H</b>

HXA039H




**Motor operator**

Description	Pack qty.	Art No.
Motor operator x250 24V DC	1	<b>HXB040H</b>
Motor operator x250 230-240VAC	1	<b>HXB042H</b>

HXB040H

**Interlocking**

Description	Pack qty.	Art No.
Interlocking wire type x250	1	<b>HXB065H</b>
Interlock front cover x250	1	<b>HXB066H</b>
Interlock cable 1m(P160-x/h/P250..1000)	1	<b>HXB070H</b>
Interlock cable 1.5m(P160-x/h250..1000)	1	<b>HXB071H</b>



HXB065H

**Electrical interlock**

Description	Pack qty.	Art No.
Elec. interlock Motor A (x/P/h 250)	1	<b>HXB068H</b>
Elec.interlock MotB(x/P/h250-h400..1000)	1	<b>HXB069H</b>



HXB068H

**Collar terminals**

Description	Pack qty.	Art No.
Collar terminal x250 Al/Cu 3P	1	<b>HYB001H</b>
Collar terminal x250 Al/Cu 4P	1	<b>HYB002H</b>
Collar term Al 1x95-240mm <sup>2</sup> (x250/h250) 3P	1	<b>HYB005H</b>
Collar term Al 1x95-240mm <sup>2</sup> (x250/h250) 4P	1	<b>HYB006H</b>



HYB001H

**Extended connections**


Description	Pack qty.	Art No.
Straight extension (x/P250) 4P	1	<b>HYB010H</b>
Spreader (x/P250-P250) 3P	1	<b>HYB011H</b>
Spreader (x250-P250) 4P	1	<b>HYB012H</b>



HYB010H

**Interphase barrier**

Description	Pack qty.	Art No.
Interphase barrier (x250-h250TM) 3/4P	1	<b>HYB019H</b>



HYB019H



**Terminal covers**

HYB021H

Description	Pack qty.	Art No.
Terminal cover x250 3P long	1	<b>HYB021H</b>
Terminal cover x250 4P long	1	<b>HYB022H</b>
Terminal cover x250 3P spreader	1	<b>HYB023H</b>
Terminal cover x250 4P spreader	1	<b>HYB024H</b>
Terminal cover x250 3P short	1	<b>HYB025H</b>
Terminal cover x250 4P short	1	<b>HYB026H</b>
Terminal cover for collar term. x250 3P	1	<b>HYB027H</b>
Terminal cover for collar term. x250 4P	1	<b>HYB028H</b>



**Rear connections**

HYB031H

Description	Pack qty.	Art No.
Rear connection (x/P250-P250) 3P	1	<b>HYB031H</b>
Rear connection (x/P250-P250) 4P	1	<b>HYB032H</b>



**Connection kit**

HYA035H

Description	Pack qty.	Art No.
Connecting kit 3P/4P	1	<b>HYA035H</b>



**Ring lugs**

HYA088H

Description	Pack qty.	Art No.
Ring lug D8,5 3/4P 35mm <sup>2</sup> (x/P160-x/P250)	1	<b>HYA088H</b>
Ring lug D8,5 3/4P 50mm <sup>2</sup> (x/P160-x/P250)	1	<b>HYA089H</b>
Ring lug D8,5 3/4P 70mm <sup>2</sup> (x/P160-x/P250)	1	<b>HYA090H</b>
Ring lug D8,5 3/4P 95mm <sup>2</sup> (x/P160-x/P250)	1	<b>HYA091H</b>
Ring Lug D:8,5 3P/4P for cable 120mm <sup>2</sup>	1	<b>HYB092H</b>
Ring Lug D:8,5 3P/4P for cable 150mm <sup>2</sup>	1	<b>HYB094H</b>



HNG200U

**MCCBs h3 h250 3 pole 50 kA**

Description	Pack qty.	Art No.
MCCB h250 3P 50kA 200A TM	1	<b>HNG200U</b>
MCCB h250 3P 50kA 250A TM	1	<b>HNG250U</b>

**MCCBs h3 h250 4 pole 50 kA**

Description	Pack qty.	Art No.
MCCB h250 4P 50kA 200A TM	1	<b>HNG201U</b>
MCCB h250 4P 50kA 250A TM	1	<b>HNG251U</b>

## MCCBs h3 h250 3 pole 50 kA

Description	Pack qty.	Art No.
MCCB h250 3P 50kA 40A LSI	1	<b>HNC040H</b>
MCCB h250 3P 50kA 125A LSI	1	<b>HNC125H</b>
MCCB h250 3P 50kA 250A LSI	1	<b>HNC250H</b>



HNC040H

## MCCBs h3 h250 4 pole 50 kA

Description	Pack qty.	Art No.
MCCB h250 4P 50kA 40A LSI	1	<b>HNC041H</b>
MCCB h250 4P 50kA 125A LSI	1	<b>HNC126H</b>
MCCB h250 4P 50kA 250A LSI	1	<b>HNC251H</b>



HNC041H

## MCCBs h3 h250 3 pole 70 kA

Description	Pack qty.	Art No.
MCCB h250 3P 70kA 40A LSI	1	<b>HEC040H</b>
MCCB h250 3P 70kA 125A LSI	1	<b>HEC125H</b>
MCCB h250 3P 70kA 250A LSI	1	<b>HEC250H</b>



HEC040H

## MCCBs h3 h250 4 pole 70 kA


Description	Pack qty.	Art No.
MCCB h250 4P 70kA 40A LSI	1	<b>HEC041H</b>
MCCB h250 4P 70kA 125A LSI	1	<b>HEC126H</b>
MCCB h250 4P 70kA 250A LSI	1	<b>HEC251H</b>



HEC041H

## Base for detachable MCCBs

Description	Pack qty.	Art No.
Plug-in Base h250 LSI 3P	1	<b>HYC200H</b>
Plug-in Base h250 LSI 4P	1	<b>HYC201H</b>



HYC200H



HXC021H

**Auxiliary contacts**

Description	Pack qty.	Art No.
AX contact 1NO+1NC 230VAC(h250...1600)	1	<b>HXC021H</b>
Alarm contact 1NO+1NC 230V(h250...1600)	1	<b>HXC024H</b>
AX low lvl. 1NO+NC 125VAC(x/P160...x/P630)	1	<b>HXA025H</b>
AL low lvl. 1NO+NC 125VAC(x/P160...x/P630)	1	<b>HXA026H</b>



HXC001H

**Shunt trip release**

Description	Pack qty.	Art No.
Shunt trip Release 24V DC(h250...1000)	1	<b>HXC001H</b>
Shunt trip Release 48V DC(h250...1000)	1	<b>HXC002H</b>
SHT trip Release 100-120VAC(h250...1000)	1	<b>HXC003H</b>
SHT trip Release 200-240VAC(h250...1000)	1	<b>HXC004H</b>
SHT trip Release 380-450VAC(h250...1000)	1	<b>HXC005H</b>
Shunt trip Release 110V DC(h250...1000)	1	<b>HXC008H</b>



HXC011H

**Undervoltage release**

Description	Pack qty.	Art No.
Undervolt. Release 24V DC(h250...630)	1	<b>HXC011H</b>
Undervolt. Release 100-120VAC(h250...630)	1	<b>HXC013H</b>
Undervolt. Release 100-120VDC(h250...630)	1	<b>HXC018H</b>
Undervolt. Release 200-240VDC(h250...630)	1	<b>HXC019H</b>



HXC051H

**UVR delayed h250-h630 24V DC**

Description	Pack qty.	Art No.
UVR delayed h250-h630 24V DC	1	<b>HXC051H</b>
UVR delayed 500ms h250 110-120V AC	1	<b>HXC053H</b>
UVR delayed h250-h630 220-240V AC	1	<b>HXC054H</b>
UVR delayed h250-h630 380-415V AC	1	<b>HXC055H</b>



HXC030H

**Direct rotary handles**

Description	Pack qty.	Art No.
Direct rotary handle H250	1	<b>HXC030H</b>

**Extended rotary handles**

Description	Pack qty.	Art No.
Extended rotary handle x250	1	<b>HXB031H</b>



HXB031H

**Padlock**

Description	Pack qty.	Art No.
Padlock H250	1	<b>HXC039H</b>



HXC039H

**Motor operators**


Description	Pack qty.	Art No.
Motor operator h250 24V DC	1	<b>HXC040H</b>
Motor operator h250 230-240VAC	1	<b>HXC042H</b>



HXC040H

**OCR sealing cover**

Description	Pack qty.	Art No.
Interlocking wire type x250	1	<b>HXB065H</b>
Interlock front cover x250	1	<b>HXB066H</b>
Interlock cable 1m(P160-x/h/P250..1000)	1	<b>HXB070H</b>
Interlock cable 1.5m(P160-x/h250..1000)	1	<b>HXB071H</b>



HXB065H

**Electrical interlock for Motor type A**

Description	Pack qty.	Art No.
Elec. interlock Motor A (x/P/h 250)	1	<b>HXB068H</b>
Elec.interlock MotB(x/P/h250-h400..1000)	1	<b>HXB069H</b>



HXB068H





HYC250H

**Connection for auxiliaries**

Description	Pack qty.	Art No.
PM Aux Term. panel(P160/250-h250..1000)	1	<b>HYC250H</b>
PM Aux Term. 2wires(P160-250/h250..1000)	1	<b>HYC352H</b>
PM Aux Term. 3wires(P160-250/h250..1000)	1	<b>HYC353H</b>



HYC003H

**Connection terminals**


Description	Pack qty.	Art No.
Collar terminal H250 Cu 3P	1	<b>HYC003H</b>
Collar terminal H250 Cu 4P	1	<b>HYC004H</b>
Collar term Al 1x95-240mm <sup>2</sup> (x250/h250) 3P	1	<b>HYB005H</b>
Collar term Al 1x95-240mm <sup>2</sup> (x250/h250) 4P	1	<b>HYB006H</b>



HYC010H

**Extended connection**

Description	Pack qty.	Art No.
Extended connection H250 4P collar	1	<b>HYC010H</b>
Spreader H250 3P collar	1	<b>HYC011H</b>
Spreader (x250-P250) 4P	1	<b>HYB012H</b>



HYB019H

**Interphase barrier**

Description	Pack qty.	Art No.
Interphase barrier (x250-h250TM) 3/4P	1	<b>HYB019H</b>
Interphase barrier h250 3/4P	1	<b>HYC019H</b>



HYC021H

**Terminal cover**

Description	Pack qty.	Art No.
Terminal cover H250 LSI 3P long	1	<b>HYC021H</b>
Terminal cover H250 3P long TM	1	<b>HYG021H</b>
Terminal cover H250 3P short	1	<b>HYC025H</b>
Terminal cover for collar term. h250 3P	1	<b>HYC027H</b>
Terminal cover H250 LSI 4P long	1	<b>HYC022H</b>
Terminal cover H250 4P short	1	<b>HYC026H</b>
Terminal cover for collar term. h250 4P	1	<b>HYC028H</b>

**Rear connection**

Description	Pack qty.	Art No.
Rear connexion H250 3P	1	<b>HYC031H</b>
Rear connexion H250 4P	1	<b>HYC032H</b>



HYC031H

**Connection kit**

Description	Pack qty.	Art No.
Connecting kit 3P/4P	1	<b>HYA035H</b>



HYA035H

**OCR sealing cover**

Description	Pack qty.	Art No.
OCR Sealing cover h250 LSI	1	<b>HYC041H</b>
OCR Sealing cover h250 TM	1	<b>HYG041H</b>