

Blocks and terminals

	Page
Junction blocks	3
Junction blocks	4
Brass terminals	6
Bases for brass terminals, rails for connection blocks and terminals	7



K018

Junction blocks


Description	Pack qty.	Art No.
Branch terminal, universZ, 1x25-4 x16mm ²	20	K018
Branch terminal, universZ, 2p, 1x25 ² -4 x16 ²	10	K023
Branch terminal, universZ, 4p, 1x25 ² -4 x16 ²	5	K024
Branch terminal, universZ, 5p, 1x25 ² -4 x16 ²	5	K025
Main line branch term. 1p. 1x35mm ² -4x25mm ²	4	K037



KR95P

Junction terminals

Description	Pack qty.	Art No.
DIN rail terminal 25-95mm ²	1	KR95P
DIN rail terminal 35-150mm ²	1	KR15P



K010

Connecting bars

Description	Pack qty.	Art No.
Connect.clamp, universZ, 2x5x4mm	20	K010



K085

Grounding connection

Description	Pack qty.	Art No.
Grounding connection-separate-wedges	10	K085

Phase terminals


Description	Pack qty.	Art No.
Feed-through terminal -phase, 2,5mm ²	100	KXA02LH
Feed-through terminal-phase, 4mm ²	100	KXA04LH
Feed-through terminal -phase, 10mm ²	50	KXA10L
Feed-through terminal-phase, 16mm ²	50	KXA16L
Feed-through terminal-phase, 35mm ²	20	KXA35L
Feed-through terminal-phase , 70mm ²	20	KXB70LH
Feed-through terminal-phase, 150mm ²	10	KXB150LH



KXA02LH

Neutral terminals

Description	Pack qty.	Art No.
Feed-through terminal-N, 2,5mm ²	100	KXA02NH
Feed-through terminal-N, 4mm ²	100	KXA04NH
Feed-through terminal -N, 10mm ²	50	KXA10N
Feed-through terminal-N, 16mm ²	50	KXA16N
Feed-through terminal-N, 35mm ²	20	KXA35N
Feed-through terminal-N, 70mm ²	20	KXB70NH
Feed-through terminal-N, 150mm ²	10	KXB150NH



KXA02NH

Earth terminals PE

Description	Pack qty.	Art No.
Earth terminal, 2,5mm ²	100	KXA02E
Earth terminal 10mm ²	50	KXA10E
Earth terminal, 16mm ²	50	KXA16E
Earth terminal, 70mm ²	20	KXB70E
Earth terminal, 35mm ²	20	KXB35E



KXA02E

Blocking brackets

Description	Pack qty.	Art No.
Endplate for KXA02LH, KXA04LH	10	KWE01G
Endplate for KXA10L , KXA16L	10	KWE04G
Endplate for KXA35L	10	KWE03G




KWE01G

End bracket

Description	Pack qty.	Art No.
End bracket until 35mm ²	100	KWB01
End bracket until 150qmm ²	100	KWB02




KWB01



Equipotential bridgings

Description	Pack qty.	Art No.
Jumper insulated, 2,5mm ² , 10-way	10	KWJ02B10
Jumper insulated, 4mm ² , 10-way	10	KWJ04B10
Jumper insulated, 10mm ² , 10-way	10	KWJ10B10

KWJ02B10



Marking strips

Description	Pack qty.	Art No.
Marking Clip - Box (0-9)	1	KWL001
Marking strips 1-100	1	KWL002
Marking strips 101-200	1	KWL003
Marking strip L1, L2, L3, N, PE	1	KWL004

KWL001

Brass terminals with base neutral

Description	Pack qty.	Art No.
Brass terminal, 4x10mm ² 3x16mm ² , N	50	KM07N
Brass terminal, 5x10mm ² 5x16mm ² , N	20	KM10A
Brass terminal, 5x10mm ² 5x16mm ² , N	20	KM11N
Brass terminal, 8x10mm ² 2x16mm ² , N	20	KM10N
Brass terminal, 7x10mm ² 6x16mm ² , N	20	KM13N
Brass terminal, 1x25mm ² 8x10mm ² 8x16mm ² , N	20	KM17N
Brass terminal, 1x25 ² 13x10 ² 11x16 ² , N	20	KM25N



KM07N

Brass terminals with base earth


Description	Pack qty.	Art No.
Brass terminal, 4x10mm ² 3x16mm ² , Earth	50	KM07E
Brass terminal, 5x10mm ² 5x16mm ² , Earth	20	KM10B
Brass terminal, 5x10mm ² 5x16mm ² , Earth	20	KM11E
Brass terminal, 8x10mm ² 2x16mm ² , Earth	20	KM10E
Brass terminal, 7x10mm ² 6x16mm ² , Earth	20	KM13E
Brass terminal, 1x25 ² 5x10 ² 5x16 ² , Earth	20	KM11B
Brass terminal, 1x25 ² 8x10 ² 8x16 ² , Earth	20	KM17E
Brass terminal, 1x25 ² 13x10 ² 11x16 ² , Earth	20	KM25E



KM07E

Brass terminals with base phase

Description	Pack qty.	Art No.
Brass terminal, 2x10mm ² /2x16mm ² , Phase	50	KM04L
Brass terminal, 4x10mm ² 4x16mm ² , Phase	20	KM08L
Brass terminal, 4x10mm ² 3x16mm ² , Phase	50	KM07L
Brass terminal, 5x10mm ² - 5x16mm ²	20	KM10C
Brass terminal, 7x10mm ² 4x16mm ² , Phase	20	KM11L
Brass terminal, 8x10mm ² 2x16mm ² , Phase	20	KM10L



KM04L

Brass terminals without base

Description	Pack qty.	Art No.
Brass terminal, 30mm, 2x10mm ² - 2x16mm ²	10	K140
Brass terminal, 49mm, 4x10mm ² - 3x16mm ²	10	K142
Brass terminal, 67mm, 5x10mm ² - 5x16mm ²	10	K143
Brass terminal, 73mm, 6x10mm ² - 5x16mm ²	10	K144
Brass terminal, 8x10mm ² - 2x16mm ²	10	K145
Brass terminal, 85mm, 7x10mm ² - 6x16mm ²	10	K148
Brass terminal, 85mm, 1x25mm ² - 5x10/16mm ²	10	K151
TERM.STRIP 121MM 1X25-4X16-12X10MM ²	10	K156
Brass terminal 1x25mm ² -11x16mm ² -13x10mm ²	10	K158
Brass terminal 1x25mm ² - 8x16mm ² -31x10mm ²	10	K159
Term.strip 482mm 78x10/16mm	10	K160F
Term.strip 992mm 163x10/16mm	10	K162F



K140

Bases

Description	Pack qty.	Art No.
Mounting base f. brass terminals, blue	10	KZ012
Mounting base f. brass terminals, green	10	KZ013
Mounting base f. brass terminals, brown	10	KZ014



KZ012



Flat bar supports for terminal strips

Description	Pack qty.	Art No.
#NV	50	A08900

A089



Pinch carriers

Description	Pack qty.	Art No.
Terminal carrier, Univers, L250 mm	10	UT91A


UT91A



Brass terminal support

Description	Pack qty.	Art No.
FLAT BAR 12X2MM LENGTH 2 M.	10	A09000

A090



Rail fixing clips

Description	Pack qty.	Art No.
Fixing spring f.DIN rail 10pcs, 20mm wide	10	KZ060F
Fixing spring f. DIN rail, 10mm wide	50	KZ061

KZ060F



Symmetrical rails

Description	Pack qty.	Art No.
SYMMETRICAL DIN RAIL 2M	20	A08800
SYMMETRICAL DIN RAIL 10MM 2M	20	A09800
SYMMETRICAL DIN RAIL 15MM 2M	10	A09900

A09900

Asymmetrical rails


Description	Pack qty.	Art No.
Perforated rail DIN, Venezia, 15x2000 mm	10	A099E
Perforated DIN-rail, Venezia, 15x2000 mm	10	A099B



A099E

DIN rail

Description	Pack qty.	Art No.
Profile rail, Venezia, 15x2000 mm	10	A099C



A099C

Special nuts

Description	Pack qty.	Art No.
Nut for profile rail DIN, Venezia, M6	25	A099D



A099D

Asymmetrical rail

Description	Pack qty.	Art No.
ASYMMETRICAL DIN RAIL 2M	10	A05000



A050

Screw

Description	Pack qty.	Art No.
Tapping screw 3,5x12,0 +/- PZ1	1	KZ062



KZ062