



HED631H

## MCCB h630 4P 70kA 630A LSI

Product Datasheet

### Architecture

Type of order	Toggle
Number of poles	4 P
Type of pole	4P4D N:0/50/100%

### Functions

Complete device with protection unit	yes
Trip Unit	LSI
Integrated earth fault protection	no

### Compatibility

Compatible with DIN rail mounting	no
-----------------------------------	----

### Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	no

### Electric current

Rated current	630 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	20 kA
Thermal protection nob setting xIN	0,4 / 0,5 / 0,63 / 0,8 / 0,9 / 0,95 / 1
Thermal setting current on neutral pole	0 / 0,5 / 1 In
Breaking capacity on 1 pole for IT 230V NF 60947-2	60 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	71 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	65 kA

**Current correction factors**

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

**Power**

Total power loss under I <sub>N</sub>	120 W
Power loss per pole at I <sub>n</sub>	40 W

**Tripping**

Trip mode	LSI
Thermal protection trip time	5 / 10 / 11 / 16 / 21 ms
Time of response when opening	10 ms

**Electrical specifications**

Magnetic trip delay time	100 to 200 ms
--------------------------	---------------

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

**Installation, mounting**

Tightening torque	22Nm
DIN rail mounting with optional adaptor	no

**Connection**

Connection cross-sect. flexible conductor	35 / 240mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 240mm <sup>2</sup>
Connection	Front connection
Type of connection	Terminal

**Settings**

Range of the magnetic adjustment	3500 / 4410 / 5600 / 6300 / 6300 / 6300 / 6300 / 6300 A
Magnetic protection nob setting xI <sub>N</sub>	2,5 / 5 / 8
Setting type I <sub>n</sub> or I <sub>th</sub>	I <sub>r</sub> Th

**Equipment**

Motor drive optional	yes
----------------------	-----

**Use cases**

Category of use	A
-----------------	---

**Standards**

Standard text	IEC 60947-2
European directive WEEE	concerned

**Safety**

Protection index IP	IP4X
---------------------	------

**Use conditions**

Operating temperature	-25...70 °C
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-35...70 °C