


NCN320A



NCN320A

MCB 3P 10kA/15kA C-20A 3M

Product Datasheet

Architecture

| | |
|---------------------------|-----------------|
| Neutral position | without neutral |
| Number of protected poles | 3 |
| Number of poles | 3 P |
| Type of pole | 3 P |
| Fixing mode | Din-Rail |
| Curve | C |

Functions

| | |
|----------------------------------|----|
| Concurrently switching N-neutral | no |
|----------------------------------|----|

Compatibility

| | |
|-----------------------------------|-----|
| Compatible with DIN rail mounting | yes |
|-----------------------------------|-----|

Controls and indicators

| | |
|----------------------|----|
| With fault indicator | no |
|----------------------|----|

Connectivity

| | |
|---|------------------|
| Top connection alignment for modular devices | Aligned terminal |
| Bottom connection alignment for modular devices | Aligned terminal |

Main electrical features

| | |
|---|-------|
| Rated short circuit breaking capacity Icn AC according IEC60898-1 | 10 kA |
| Rated operational voltage Ue | 400 V |
| Type of supply voltage | AC |

Voltage

| | |
|------------------------------------|--------|
| Rated insulation voltage | 500 V |
| Rated impulse withstand voltage | 6000 V |
| Minimum threshold voltage (Ue min) | 12 V |

Electric current

| | |
|--|----------------|
| Rated current | 20 A |
| Rated service breaking capacity Ics AC according IEC 60898-1 | 7,5 kA |
| min/maxi threshold value of the AC thermal operation | 1,13 / 1,45 In |
| Magnetic regulating current | 5 / 10 In |
| min/maxi threshold value of the DC magnetic operation | 7 / 15 In |
| min/maxi threshold value of the DC thermal operation | 1,13 / 1,45 In |
| Rating current -10°C according to IEC 60947 | 26,27 A |
| Rating current -15°C according to IEC 60947 | 26,72 A |
| Rating current -20°C according to IEC 60947 | 27,17 A |
| Rating current -25°C according to IEC 60947 | 27,61 A |
| Rating current -5°C according to IEC 60947 | 25,8 A |
| Rating current 0°C according to IEC 60947 | 25,33 A |
| Rating current 10°C according to IEC 60947 | 24,36 A |

| | |
|---|---------|
| Rating current 150°C according to IEC 60947 | 23,86 A |
| Rating current 20°C according to IEC 60947 | 23,34 A |
| Rating current 25°C according to IEC 60947 | 22,82 A |
| Rating current 30°C according to IEC 60947 | 22,29 A |
| Rating current 35°C according to IEC 60947 | 21,74 A |
| Rating current 40°C according to IEC 60947 | 21,17 A |
| Rating current 45°C according to IEC 60947 | 20,6 A |
| Rating current 5°C according to IEC 60947 | 24,85 A |
| Rating current 50°C according to IEC 60947 | 20 A |
| Rating current 55°C according to IEC 60947 | 19,34 A |
| Rating current 60°C according to IEC 60947 | 18,65 A |
| Rating current 65°C according to IEC 60947 | 17,94 A |
| Rating current 70°C according to IEC 60947 | 17,2 A |
| Rated service breaking capacity Ics under 220V AC according IEC 60947-2 | 15 kA |
| Rated service breaking capacity Ics under 230V AC according IEC 60947-2 | 15 kA |
| Rated service breaking capacity Ics under 240V AC according IEC 60947-2 | 15 kA |
| Rated service breaking capacity Ics under 380V AC according IEC 60947-2 | 7,5 kA |
| Rated service breaking capacity Ics under 400V AC according IEC 60947-2 | 7,5 kA |
| Rated service breaking capacity Ics under 415V AC according IEC 60947-2 | 7,5 kA |
| Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1 | 10 kA |
| Rated short circuit breaking capacity Icn under 400V AC according IEC60898-1 | 10 kA |
| Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2 | 30 kA |
| Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2 | 30 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2 | 15 kA |
| Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2 | 15 kA |
| Rated short circuit breaking capacity Icn under 240V AC according IEC 60898-1 | 10 kA |
| Rated short circuit breaking capacity Icn under 380V AC according IEC 60898-1 | 10 kA |
| Rated short circuit breaking capacity Icn under 415V AC according IEC 60898-1 | 10 kA |
| Rated service breaking capacity Ics under 220V AC according IEC 60898-1 | 7,5 kA |
| Rated service breaking capacity Ics under 230V AC according IEC 60898-1 | 7,5 kA |
| Rated service breaking capacity Ics under 240V AC according IEC 60898-1 | 7,5 kA |
| Rated service breaking capacity Ics under 380V AC according IEC 60898-1 | 7,5 kA |
| Rated service breaking capacity Ics under 400V AC according IEC 60898-1 | 7,5 kA |
| Rated service breaking capacity Ics under 415V AC according IEC 60898-1 | 7,5 kA |
| Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2 | 30 kA |
| Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2 | 15 kA |

Electric current / temperature

| | |
|----------------------|---------|
| Rating current -25°C | 24,78 A |
| Rating current -20°C | 24,38 A |
| Rating current -15°C | 23,98 A |
| Rating current -10°C | 23,57 A |
| Rating current -5°C | 23,16 A |
| Rating current 0°C | 22,73 A |
| Rating current 5°C | 22,3 A |
| Rating current 10°C | 21,86 A |
| Rating current 25°C | 20,48 A |
| Rating current 30°C | 20 A |
| Rating current 35°C | 19,48 A |
| Rating current 40°C | 18,94 A |
| Rating current 45°C | 18,39 A |
| Rating current 50°C | 17,81 A |
| Rating current 55°C | 17,22 A |
| Rating current 60°C | 16,61 A |
| Rating current 65°C | 15,98 A |
| Rating current 70°C | 15,32 A |

Current correction factors

| | |
|---|------|
| Correction factor of rating current for 2 devices placed side-by-side | 1 |
| Correction factor of rating current for 3 devices placed side-by-side | 0,95 |
| Correction factor of rating current for 4 and 5 devices placed side-by-side | 0,9 |
| Correction factor of rating current for 6 devices placed side-by-side | 0,85 |
| Correction factor of magnetic tripping with 100 Hz | 1,1 |
| Correction factor of magnetic tripping with 200 Hz | 1,2 |
| Correction factor of magnetic tripping with 400 Hz | 1,5 |
| Correction factor of magnetic tripping with 60 Hz | 1,1 |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|---|--------|
| Maximum power loss per pole according to the product standard | 4,5 W |
| Total power loss under I _N | 8,04 W |
| Power loss per pole at I _n | 2,72 W |

Endurance

| | |
|--|-------|
| Electric endurance in number of cycles | 4000 |
| Number of mechanical operations | 20000 |

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 70 mm |
| Height of installed product | 83 mm |
| Width of installed product | 52,5 mm |

Installation, mounting

| | |
|---|------------|
| Type of top connection for modular devices | with screw |
| Tightening torque | 2,8Nm |
| Type of top rail clip for modular devices | NA |
| Type of bottom rail clip for modular devices | plastic |
| Type of Bottom Connection for modular devices | Blconnect |
| Top removability for modular devices | yes |
| Bottom removability for modular devices | yes |
| Suitable for flush-mounting | yes |
| 360° product mounting position | yes |

Connection

| | |
|--|------------------------|
| Connection cross-section at output with screw, for flexible conductor | 1 / 25 mm ² |
| Connection cross-section at output with screw, for massive conductor | 1 / 35 mm ² |
| Connection cross-section for rigid conductor, upstream terminals with screws | 1 / 35 mm ² |
| Connection cross-section of the access with screws, with flexible conductor | 1 / 25 mm ² |
| Downstream cage clamp delivery status | opened |
| Upstream cage clamp delivery status | opened |

Equipment

| | |
|---------------------------------------|-----|
| Can be accessorized | yes |
| With transparent product label holder | yes |

Standards

| | |
|--|-------------------------|
| Standard text | EN 60898-1, IEC 60947-2 |
| European directive WEEE | concerned |
| Product categories described in the W3E directive 2012/19/EU | Category 5 |

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|--|-------------|
| Operating temperature | -25...70 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Class of energy limitation I ² t | 3 |
| Altitude | 2000 m |
| Storage/transport temperature | -25...80 °C |

temperatur

Temperature of calibration

50 °C
