



CDB463F

RCCB 4P 63A 30mA B

Product Datasheet

Architecture

Neutral position	left
Number of poles	4 P
Fixing mode	Din-Rail

Functions

Sealable	no
----------	----

Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

Controls and indicators

Ground fault signalisation	yes
----------------------------	-----

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	30 mA
Rated current	63 A
Withstand not tripping on 8-20 μ s wave	3 kA
Breaking and opening capacity	0,63 kA
Rated conditional short-circuit current Inc according to EN 61008-1	10 kA

Electric current / temperature

Rating current 30°C	63 A
---------------------	------

Frequency

Frequency	50 Hz
-----------	-------

Power

Total power loss under IN	9,3 W
Power loss per pole at In	3,1 W

Tripping

Protected against nuisance tripping	yes
Short-time delayed tripping	no

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	10000

Dimensions

Depth of installed product	70 mm
Height of installed product	85 mm
Construction size (DIN 43880)	1

Installation, mounting

Type of top connection for modular devices	with screw
Tightening torque	3
Type of Bottom Connection for modular devices	Blconnect
Top removability for modular devices	no
Bottom removability for modular devices	yes

Connection

Connection cross-section at output with screw, for massive conductor	1,5 / 50 mm ²
Connection cross-sect. flexible conductor	1,5 / 50mm ²
Connection cross-sect. rigid cable	1,5 / 50mm ²
Connection cross-section for rigid conductor, upstream terminals with screws	1,5 / 50 mm ²
Connection cross-section of the access with screws, with flexible conductor	1,5 / 16 mm ²
Connection cross-section of input and output with screws, for massive conductors	1,5 / 50 mm ²
Connection cross section of access and exit with screws, for flexible conductor	1,5 / 16 mm ²
Type of connection	with screw

Equipment

With interlocking device	no
With transparent product label holder	yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
Residual current type	B

Use conditions

Operating temperature	-25...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-25...40 °C